

Product Information Sheet

SpillSmart Spill Kit 240lt Hazchem

ABSORBENT ♦ FAST ACTING ♦ HIGH ABSORBENCY

IQ have put together a range of emergency response Spill Kits to cater for your varying spill response needs.

The SpillSmart Hazchem Spill Kits contains inert products that will effectively and efficiently absorb hazardous chemical spills, including most acids, coolants, solvents and oils.

There are a number of factors and issues to consider when selecting the correct spill kit and response equipment. Deciding on the correct type and size of equipment for the appropriate risk response is a consideration.

There is a range of SpillSmart Spill Kits available to suit the type and size of fluid spilt, depending on the particular situation. Determine which liquids may be spilt and then determine which type of absorbent products you require.

The SpillSmart 240lt Hazchem, wheelie bin Spill Kit combines premium absorbent and socks with pads and pillows, all packed in a portable wheelie bin. The Hazchem Spill Kit has necessary absorbent products for effective spill response to most dangerous spills. The kits are designed for use in workshops, factories, laboratories or wherever hazardous chemicals are stored, handled or may be spilt

The convenience of storing these products in a robust wheelie bin ensures that all products are readily available, should an unforeseen spill occur.

Be wary of some other products making unrealistic claims about absorbency and disposal.

PART #	DESCRIPTION	QTY
<i>PWB240B</i>	240lt Blue Wheelie Bin	1
<i>ES-PPHAZ400-P</i>	SpillSmart Poly Pads Hazchem 48cm x 43cm x Heavy Weight Dimpled & Perforated	40
<i>ES-A-HAZ-30</i>	SpillSmart Hazsorb 30lt	3
<i>ES-SPHZ-75-1.2</i>	SpillSmart Polypropylene Socks Hazchem 1.2m x 75mm	4
<i>ES-SPHZ-75-3</i>	SpillSmart Polypropylene Socks Hazchem 3m x 75mm	1
<i>ES-P-HAZ-A</i>	SpillSmart Pillow Hazchem 45cm x 45cm	1
<i>ES-G-NL</i>	Pair of Nitrile Gloves	2
<i>ES-WB</i>	SpillSmart Contaminated Waste Bags 450mm x 720mm	10
	Dust pan and brush	1
	Spill Kit sticker	1
	Spill Kit Instructions	1

DIRECTIONS FOR USE:

- Assess the liquid that was spilt before applying absorbent (consult MSDS for safety precautions)
- Contain the spill using Hazsorb or absorbent socks
- Apply Hazsorb to cover the spill
- The spill/Hazsorb mix should appear dry. If not, add more Hazsorb
- Using a stiff broom, sweep Hazsorb over the spill area
- Again, if the mix does not appear dry, or if there is an oily film on the surface, use additional Hazsorb
- Use the pads and pillows for any continuing leaks and to wipe areas not cleaned by the Hazsorb
- Dispose of as per Government regulations
- Action an incident report
- Contact your local SpillSmart distributor to replace used products

External Length	59cm
External Height	108cm
External Depth	74cm
Weight	40kg
Capacity	240lt

